

# Beckman Type P30 & P30 XL Tips

## 384 Disposable Tips

Compatible with the following Liquid Handlers:  
Biomek™ NX/FX/FXP and Multimek™

Instruments

Services & Training

Reagent Kits

Lab Supplies

### Alternative Disposable Tips

*Manufactured to stringent  
Beckman Specifications*

*Ensured Consistent Performance  
and Quality*

*OEM Corning Axygen™ Branded*

*Automation Trainer Branded Tips*

*Order From Thermo Fisher Catalog*

*No Separate Labware Definitions  
Required*



*Automation Trainer is an OEM for Corning  
Consumables from the Automation Experts you trust  
Instruments, Tools, and Services for the Simplification and  
Practical Application of Measurement Standards  
in Automated Liquid Handling and Pipetting Systems*



Beckman P30 Type



Beckman P30 XL Type

**Satisfaction Guarantee**

**Simple. Practical. Cost-effective.**

Automation Trainer LLC PO Box 2534 Sacramento, CA 95812

© 2021 Content subject to change without notice. For research use only. Not for diagnostic procedures.  
(617) 752-2288 [www.AutomationTrainer.com](http://www.AutomationTrainer.com) [support@automationtrainer.com](mailto:support@automationtrainer.com)

Rev 20210701

**Consistent Performance.  
Quality Ensured.**

# Beckman P30 & P30XL Type 384 Disposable Tips

## Description

Beckman-compatible Automation Trainer supplied liquid handling pipette tips are manufactured to strict standards to ensure quality and consistent performance. Automation control software protocol modification and separate labware definition is not required when using our tips.

## Specifications

Part Number	BP30CLXXX, BP30XLCLXXX in Automation Trainer Catalog; FX-384- and FXF-384- prefixes in Corning Catalog; Thermo Fisher Catalog Part Number's TBA Correspond to Beckman part# AP384
Color	Clear
For Use With (Equipment)	384 Multi-channel Biomek NX/FX/FXP, Multimek heads, and some i-series
Material	Polypropylene
Packaging	10 Racks/Pack, 5 Packs/Case
Variations	Non-sterile, sterile, filtered and unfiltered
Max Working Volume	30 $\mu$ L (P30), 50 $\mu$ L (P30XL)
Manufacturing	Tips are manufactured within an ISO Certified, manufacturing facility



*Lab Consumables, Instruments, Tools and Services for  
the Simplification and Practical Application of  
Measurement Standards in  
Automated Liquid Handling and Pipetting Systems*

Automation Trainer LLC PO Box 2534 Sacramento, CA 95812

© 2021 Content subject to change without notice.  
For research use only. Not for diagnostic procedures.

(617) 752-2288 [www.AutomationTrainer.com](http://www.AutomationTrainer.com) [support@automationtrainer.com](mailto:support@automationtrainer.com)